

Substation - Copper V Type T Connector

By Burndy
Catalog # [VTT3434](#)

V Style Connectors



Features

- High copper alloy T-Connector for pipe cable, cable tap
- DURIMUM V-Bolt clamping elements accommodate large range of cable are are particularly suited for extra flexible cable
- Twin V elements for additional joint strength against vibration and flexing on tap side

Application

Substation

Specifications

Standards - RoHS Compliance	EX
Status	
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	300 kcmil-500 kcmil
Conductor - Copper Str Run	• 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil
Conductor - Connection Combination	Cable to Cable
Conductor - Copper Str Tap Range	300 kcmil-500 kcmil
Conductor - Copper Str Tap	• 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil

Configuration

Physical Attribute - Number of Tap Conductors	1
---	---

Physical Attribute - Number of Run Conductors	1
Connector Type	T-Connector

Dimensions

Package Height	0.000 in
Dimension - Height mm	84.8 mm
Dimension - Height inch	3.34 in
Package Weight	0.000 lb.
Dimension - Width mm	57 mm
Dimension - Width inch	2.25 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	133 mm
Dimension - Length Overall inch	5.25 in

General

Plated	N
Material - Hardware	DURIMUM™ Silicon Bronze
One Wrench Installation	Y
UPC	621945153431
Type	Bolted Tees
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	621945153431
UPC 14 Digit GTIN	00621945153431

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)