



YA44A3DT, 1000 kcmil AL, 2-Hole NEMA, Soldered Seam

By Burndy

Catalog # [YA44A3DT](#)

1000 kcmil, AL, 2 Hole, 1/2" Stud 1-3/4" Hole Spacing, AL9CU, Solder Seam



Features

- UL486A-486B Listed and CSA Certified
- Aluminum terminals are dual rated to accommodate both copper and aluminum wire and are indicated with AL-CU on the connector - AL9CU is UL Listed 90°C, up to 35kV, AL7CU is UL Listed 75°C, up to 35kV
- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damage of the wire strands during insertion
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with wire size, die index, color code, and crimp location bands
- Factory pre-filled with PENETROX Type A13 oxide inhibitor
- Color coded end caps are factory inserted in the barrels to match the die color code and prevent foreign materials from entering the barrel
- Aluminum oxidation is not easily detected but causes resistance in a connection, it is imperative the proper preparation takes place prior to making an aluminum-to-aluminum connection

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Size	1000 KCMIL
Conductor - Material	ALUMINUM / COPPER
Wire Size	1000 KCMIL
Conductor - AL Str Size	1000 KCMIL
Conductor - AL Str Size Range	1000 kcmil
Conductor Type	CODE

Conductor - Copper Str Size Range	1000 kcmil
Conductor - Copper Str Size	1000 KCMIL

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	DUAL RATED

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.65 in
Dimension - Bolt Hole Size inch	0.52 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	2-3/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.77 in
Dimension - L Length Overall mm	197 mm
Dimension - B Length inch	2.74 in
Dimension - Outside Diameter inch	1.84 in
Dimension - D inch	3.15 in
Dimension - N inch	0.63 in
Dimension - Thread Size	1/2
Dimension - Hole Size mm	14 mm
Dimension - Bolt Size inch	0.5
Dimension - Hole Size inch	0.56
Dimension - Length Overall inch	7.76 in
Dimension - Stud Size fraction	1/2

General

Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered

Plated	Y
Color Code	Gray
Trade Name	HYLUG™
Physical Attribute - Tongue	Standard
Type	
Die Index	302
UPC	781810066133
Material	Aluminum
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810066133
UPC 14 Digit GTIN	00781810066133

Logistics	
Minimum Pack Quantity	2
Carton Quantity	2

Operational	
Temperature Rating	194

Product Assets	
Catalog [English]	
Installation Manual [English]	
Installation Manual [English]	

