




VV2A34CG1, Substation - Copper V Type Terminal

By Burndy
Catalog # [VV2A34CG1](#)

V Style Connectors



Features

- Type VVA VARILUG Terminals, for Copper Cable to Pad
- Type VVA features twin elements to secure against vibration and flexing
- High copper alloy terminal for joining a wide range of cable to equipment pads or bar
- Particularly suitable for use on extra flexible cable
- One-wrench installation

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	300 kcmil-500 kcmil
Conductor - Copper Str Size	• 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil

Configuration

Connector Type	Terminal
----------------	----------

Dimensions

Dimension - Pad Width inch	3.00 in
Dimension - Height mm	66.5 mm
Dimension - Height inch	2.62 in
Dimension - Width mm	130 mm
Dimension - Width inch	5.12 in
Dimension - L Length Overall mm	146 mm
Dimension - D inch	3.75 in
Dimension - Length Overall inch	5.75 in

General

Plated	N
Trade Name	VARILUG™
Material - Hardware	DURIUM™ Silicon Bronze
UPC	621945096905
Type	Bolted Lugs & Terminals
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	621945096905
UPC 14 Digit GTIN	00621945096905

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)