




VV2A4044N, Substation - Copper V Type Terminal

By Burndy
Catalog # [VV2A4044N](#)

V Style Connectors



Features

- Type VVA VARILUG Terminals, for Copper Cable to Pad
- Type VVA features twin elements to secure against vibration and flexing
- High copper alloy terminal for joining a wide range of cable to equipment pads or bar
- Particularly suitable for use on extra flexible cable
- One-wrench installation

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	500 kcmil-800 kcmil
Conductor - Copper Str Size	• 500 kcmil • 550 kcmil • 600 kcmil • 700 kcmil • 750 kcmil • 800 kcmil

Configuration

Connector Type	Terminal
----------------	----------

Dimensions

Dimension - Pad Width inch	4.00 in
Package Height	0.000 in
Dimension - Height mm	44.5 mm
Dimension - Height inch	1.75 in
Package Weight	0.000 lb.
Dimension - Width mm	141 mm
Dimension - Width inch	5.56 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	230 mm
Dimension - Length Overall inch	9.06 in

General

Plated	N
Trade Name	VARILUG™
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810163405
Type	Bolted Lugs & Terminals
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810163405
UPC 14 Digit GTIN	00781810163405

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)