



YAB28CG24, Compression Terminal, 1-Hole, Brazed Lug

By Burndy

Catalog # [YAB28CG24](#)

Copper Compression Terminal



Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper DLO Size Range	4/0 AWG
Conductor - Copper DLO Size	4/0 (550/#24) DLO
Conductor Size	4/0 AWG
Conductor - Copper Flex G Size Range	4/0 AWG
Conductor - Material	COPPER
Conductor - Copper Flex K Size Range	4/0 AWG
Conductor Type	CODE
Conductor - Copper Str Size Range	4/0 AWG
Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Flex H Size Range	4/0 AWG
Conductor - Copper Flex I Size Range	4/0 AWG

Configuration

Physical Attribute - Number of Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.00 in
Package Height	0.000 in

Dimension - Hole Size fraction	5/16
Dimension - Bolt Size fraction	5/16
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-11/16 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.75 in
Dimension - L Length Overall mm	76 mm
Dimension - B Length inch	1.66 in
Dimension - Outside Diameter inch	0.77 in
Dimension - D inch	2.25 in
Dimension - N inch	0.50 in
Dimension - Hole Size mm	10 mm
Dimension - Bolt Size inch	0.3125
Dimension - Hole Size inch	0.38
Dimension - Length Overall inch	3.00 in
Dimension - Stud Size fraction	5/16

General

Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Purple
Trade Name	HYLUG™
Die Index	15
UPC	621945125858
Type	Standard Barrel, Tin Plated
Material	COPPER
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	621945125858
UPC 14 Digit GTIN	00621945125858

Logistics

Pallet Quantity	1
Carton Quantity	1

Operational

Temperature Rating	194
--------------------	-----



A Hubbell brand