

YAD1414F, Uninsulated Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # [YAD1414F](#)

Uninsulated Fork Terminal For 16 - 14 AWG



Features

- Constructed of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Long brazed seam barrel and deep V groove inner serrations provide optimum conductivity reliability and holding power after crimping
- Electro-tin plating to provide durable, long-lasting corrosion resistance
- Wire range is clearly marked on terminal for easy identification
- Inspection hole for an easy visual check of wire insertion
- Long neck terminal permits easy bending and stacking of several terminals on a common stud

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards	UL486
Met	
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor Size	16 - 14 AWG
Conductor - Copper Str Size	20 AWG - 14 AWG
Range	
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Fork Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Z inch	0.39 in
Dimension - L Length Overall	23 mm
mm	
Dimension - Pad Width inch	0.47 in
Dimension - Hole Size fraction	7/25
Dimension - Bolt Size fraction	1/4
Dimension - Hole Size inch	0.28 in
Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	1/4
Dimension - Length Overall	0.92 in
inch	

General

Physical Attribute - Tongue	Fork
Type	
Trade Name	HYLUG™
Plated	Y
Feature - Barrel Type	Long
Feature - Barrel Style	Chamfered
UPC 12 Digit	781810806135
UPC 14 Digit GTIN	00781810806135
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810806135

Logistics

Minimum Pack Quantity	1000
Packaging Type	Bulk
Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)