



WCY83, WEJTAP Connector

By Burndy
Catalog # [WCY83](#)



Wejtap Assembly, Installed With Yellow Booster, Sum of diameters: 1.440 (Max), 1.288 (Min)

Features

- WEJTAP Connector installed with Yellow Power Booster

Application

For use in tap applications using large run and tap conductor sizes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	556.5-1000
Conductor - AL Str Run	• 556.5 • 600 • 636 • 650 • 700 • 715.5 • 750 • 795.5 • 800 • 874.5 • 900 • 954 • 1000
Conductor - AL Str Tap Range	4-2/0
Conductor - AL Str Tap	• 4 • 3 • 2 • 1 • 1/0 • 2/0
Conductor Type	• ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap

Conductor - ACSR Str Run Range	477.0 (30/7) Hen-795 (30/19) Mallard
Conductor - ACSR Str Run	• 477.0 (30/7) Hen • 556.5 (24/7) Parakeet • 556.5 (26/7) Dove • 556.5 (30/7) Eagle • 605 (24/7) Peacock • 605 (26/7) Squab • 605 (30/19) Teal • 636 (24/7) Rook • 636 (26/7) Grosbeak • 636 (30/19) Egret • 666.6 (24/7) Flamingo • 715.5 (54/7) Crow • 715.5 (26/7) Starling • 715.5 (30/19) Redwing • 795 (54/7) Condor • 795 (26/7) Drake • 795 (30/19) Mallard
Conductor - ACSR Str Tap Range	4 (7/1) Swanate-1/0 (6/1) Raven
Conductor - ACSR Str Tap	• 4 (7/1) Swanate • 3 (6/1) Swallow • 2 (6/1) Sparrow • 2 (7/1) Sparate • 1 (6/1) Robin • 1/0 (6/1) Raven

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.79 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	3.5 in
Package Width	0.000 in

General

Trade Name	WEJTAP™
Sub Brand	WEJTAP
UPC	781810875551
Type	Wejtap Connector
Material	Aluminum

UPC 12 Digit	781810875551	Pallet Quantity	350
UPC 14 Digit GTIN	00781810875551	Carton Quantity	5

Logistics

Minimum Pack Quantity 5



A Hubbell brand

Product Assets

[Catalog \[English\]](#)