



YAD188, Uninsulated Ring Terminal For 22 - 18 AWG, 1-Hole, #6-8 Stud

By Burndy

Catalog # [YAD188](#)

Uninsulated Ring Terminal For 22 - 18 AWG



Features

- Constructed of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Long brazed seam barrel and deep V groove inner serrations provide optimum conductivity reliability and holding power after crimping
- Electro-tin plating to provide durable, long-lasting corrosion resistance
- Wire range is clearly marked on terminal for easy identification
- Inspection hold for an easy visual check of wire insertion
- Long neck terminal permits easy bending and stacking of several terminals on a common stud

Application

For control wiring and other standard duty applications

Specifications


Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	UL467
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor Size	22 - 18 AWG
Conductor - Copper Str Size Range	22 AWG - 18 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal



Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	20 mm
Dimension - Pad Width inch	0.32 in
Package Height	0.000 in
Dimension - Hole Size fraction	8/47
Dimension - Hole Size inch	0.17 in
Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	• #6 • #8
Dimension - Z inch	0.33 in
Dimension - Bolt Size fraction	#6 - #8
Dimension - Length Overall inch	0.77 in

General

Trade Name	HYLUG™
Sub Brand	HYLUG
Physical Attribute - Tongue Type	Ring
Plated	Y
Feature - Barrel Type	Long
Feature - Barrel Style	Chamfered
Type	Ring Tongue
UPC 12 Digit	781810806210
UPC 14 Digit GTIN	00781810806210
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810806210

Logistics

Minimum Pack Quantity	900
Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)