

YAE10N112LFBOX, Nylon Locking Fork Terminal For 12 - 10 AWG

By Burndy
Catalog # [YAE10N112LFBOX](#)

Nylon Locking Fork Terminal For 12 - 10 AWG



Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

Application

For Easy Terminal Insertion And Removal

Specifications

Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	12 - 10 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor Range	#12 AWG to #10 AWG

Configuration

Connector Type Locking Fork Terminal

Dimensions

Dimension - Z inch	0.29 in
Dimension - L Length Overall mm	26 mm
Dimension - Pad Width inch	0.35 in
Dimension - Bolt Size fraction	#10
Dimension - Strip Length inch	11/32
Dimension - Stud Size fraction	• #8 • #9 • #10
Dimension - Length Overall inch	1.02 in

General

Sub Brand	INSULUG
Insulation Type	Nylon
Physical Attribute - Tongue Type	Snap Fork
Trade Name	INSULUG™
Plated	Y
Insulation	Y
Type	Long Barrel
UPC 12 Digit	781810524459
UPC 14 Digit GTIN	00781810524459
Material	Copper
Plating Type	Tin
UPC	781810524459

Logistics

Minimum Pack Quantity	1
Carton Quantity	100
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)