




YAE12Z3, Nylon Flanged Fork Terminal For 14 - 12 AWG

By Burndy
Catalog # [YAE12Z3](#)



Nylon Flanged Fork Terminal For 14 - 12 AWG

Features

- Flange fork tongue design allows fast installation as screw only has to be loosened for termination
- The flanges on the end of the fork terminal aid in preventing a slightly loose terminal from becoming fully disconnected from the screw
- Flanges make re-securing a loose terminal easier

Application

For Faster Installation While Maintaining Security If Supporting Screw Becomes Loose

Specifications

Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	• UL486 • Military Specified (Mil-Spec)
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Aircraft Size Range	AN14 - AN12
Conductor Size	14 - 12 AWG
Conductor - Copper Str Size Range	14 AWG - 12 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Flanged Fork Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Pad Width inch	0.31 in
Dimension - Hole Size fraction	8/47
Dimension - Hole Size inch	0.17 in
Dimension - Strip Length inch	21/64 in
Dimension - Stud Size inch	#6 - #8
Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.25 in
Dimension - Z inch	0.30 in
Dimension - Bolt Size fraction	#6 - #8
Dimension - Length Overall inch	1.16 in
Dimension - N inch	0.2 in

General

Insulation Type	Nylon
Trade Name	INSULUG™
Insulation	Y
Sub Brand	INSULUG
Color Code	Green
Physical Attribute - Tongue Type	Flanged Fork
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Shrouded
Type	YAE-Z, Flanged
UPC 12 Digit	781810804070
UPC 14 Digit GTIN	00781810804070
Material	Copper
Plating Type	Electro Tin
UPC	781810804070

Logistics

Minimum Pack Quantity	500
Packaging Type	Bulk
Carton Quantity	500
Pallet Quantity	99999

Operational

Temperature Rating	105° C
--------------------	--------

Product Assets

[Catalog \[English\]](#)



A Hubbell brand