



YA39A3, Al Compression, 1-Hole, 5/8" Stud, AL9CU, 750 kcmil

By Burndy

Catalog # [YA39A3](#)

750 kcmil, AL, 1-Hole, 5/8" Stud, AL9CU, Prefilled with oxide inhibitor, End Cap, Tin Plated



Features

- UL486A-486B Listed and CSA Certified
- Aluminum terminals are dual rated to accommodate both copper and aluminum wire and are indicated with AL-CU on the connector - AL9CU is UL Listed 90°C, up to 35kV, AL7CU is UL Listed 75°C, up to 35kV
- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damage of the wire strands during insertion
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with wire size, die index, color code, and crimp location bands
- Factory pre-filled with PENETROX Type A13 oxide inhibitor
- Color coded end caps are factory inserted in the barrels to match the die color code and prevent foreign materials from entering the barrel
- Aluminum oxidation is not easily detected but causes resistance in a connection, it is imperative the proper preparation takes place prior to making an aluminum-to-aluminum connection

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	ALUMINUM / COPPER
Wire Size	• 700 KCMIL • 750 KCMIL
Conductor - AL Str Size	700 KCMIL-750 KCMIL
Conductor - AL Str Size Range	700 kcmil - 750 kcmil
Conductor - Copper Str Size	• 700 KCMIL

Conductor Size	• 750 KCMIL • 700 KCMIL • 750 KCMIL
Conductor Type	CODE
Conductor - Copper Str Size Range	700 kcmil - 750 kcmil

Configuration

Physical Attribute - Number of Holes	1
Connector Type	DUAL RATED

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	2.05 in
Package Height	0.000 in
Dimension - Hole Size fraction	5/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	147 mm
Dimension - Outside Diameter inch	1.46 in
Dimension - Thread Size	5/8 in
Dimension - Hole Size mm	17.5 mm
Dimension - Hole Size inch	0.69
Dimension - Strip Length inch	2 7/8
Dimension - Stud Size inch	5/8
Dimension - Stud Size fraction	5/8
Dimension - Bolt Hole Size inch	0.66 in
Dimension - Bolt Size fraction	5/8
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	2-7/16 in
Dimension - Z inch	1.00 in
Dimension - B Length inch	2.46 in
Dimension - D inch	1.88 in
Dimension - N inch	0.88 in
Dimension - Bolt Size inch	0.63
Dimension - Length Overall inch	5.80 in

General

Trade Name	HYLUG™
Die Index	936
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Yellow
Physical Attribute - Tongue Type	Standard
Sub Brand	HYLUG
UPC	781810752067
Type	YA-A, Dual Rated
Material	ALUMINUM
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated

UPC 12 Digit	781810752067
UPC 14 Digit GTIN	00781810752067

Logistics

Pallet Quantity	1
Carton Quantity	24

Operational

Temperature Rating	194
--------------------	-----

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[English\]](#)



A Hubbell brand