

YAE14N107LFBOX, Nylon Locking Fork Terminal For 16 - 14 AWG

By Burndy

Catalog # [YAE14N107LFBOX](#)

Nylon Locking Fork Terminal For 16 - 14 AWG



Features

- Locking fork tongue design allows fast installation, screw only has to be loosened for termination
- Internal configuration of the fork prevents the terminal from coming off the screw without applying a pulling force
- Locking fork is made from a copper alloy and permits many installations while maintaining proper spring retention of forks

Application

Power Connector

Specifications

Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	16 - 14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Type	CU C Str-Size

Configuration

Connector Type	Locking Fork Terminal
----------------	-----------------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Z inch	0.30 in
--------------------	---------

Dimension - L Length Overall mm	24 mm
Dimension - Pad Width inch	0.25 in
Dimension - Bolt Size fraction	#4 - #6
Dimension - Strip Length inch	7/32 in
Dimension - Stud Size fraction	• #4 • #5 • #6
Dimension - Stud Size inch	#4 - #6
Dimension - Length Overall inch	0.93 in

General

Sub Brand	INSULUG
Insulation Type	Nylon
Color Code	Blue
Physical Attribute - Tongue Type	Locking Fork
Trade Name	INSULUG™
Plated	Y
Feature - Barrel Type	Standard
Insulation Type	Long Barrel
UPC 12 Digit	781810524527
UPC 14 Digit GTIN	00781810524527
Material	Copper
Plating Type	Unplated
UPC	781810524527

Logistics

Minimum Pack Quantity	100
Carton Quantity	100
Pallet Quantity	1

Operational

Temperature Rating	105° C
--------------------	--------

Product Assets

[Catalog \[English\]](#)