

YAE14N109BFBOX, Nylon Block Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # [YAE14N109BFBOX](#)

Nylon Block Fork Terminal For 16 - 14 AWG



Features

- Permits rapid, easy installation of the terminal under the screw head without complete removal of the screw
- Designed to fit securely into terminal blocks

Application

Power Connector

Specifications

Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	16 - 14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Type	CU C Str-Size

Configuration

Connector Type	Block Fork Terminal
----------------	---------------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Z inch	0.79 in

Dimension - L Length Overall mm	24 mm
Dimension - Pad Width inch	0.32 in
Package Height	0.000 in
Dimension - Bolt Size fraction	#8 - #10
Dimension - Strip Length inch	3/16 in
Dimension - Stud Size inch	#8 - #10
Dimension - Length Overall inch	0.95 in

General

Sub Brand	INSULUG
Insulation Type	Nylon
Color Code	Blue
Physical Attribute - Tongue Type	Block Fork
Trade Name	INSULUG™
Plated	Y
Feature - Barrel Type	Standard
Insulation Type	YAE-N
UPC 12 Digit	781810524558
UPC 14 Digit GTIN	00781810524558
Material	Copper
Plating Type	Unplated
UPC	781810524558

Logistics

Minimum Pack Quantity	100
Carton Quantity	100
Pallet Quantity	99999

Operational

Temperature Rating	105° C
--------------------	--------

Product Assets

[Catalog \[English\]](#)