


YAE14Z3M, Nylon Flanged Fork Terminal For 16 - 14 AWG (Tape Mounted)

By Burndy
Catalog # [YAE14Z3M](#)



Nylon Flanged Fork Terminal For 16 - 14 AWG (Tape Mounted)

Features

- Flange fork tongue design allows fast installation as screw only has to be loosened for termination
- The flanges on the end of the fork terminal aid in preventing a slightly loose terminal from becoming fully disconnected from the screw
- Flanges make re-securing a loose terminal easier

Application

Power Connector

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Industry Standard(s)	• UL486 • Military Specified (Mil-Spec)
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Aircraft Size Range	AN16 - AN14
Conductor Size	16 - 14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Flanged Fork Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - B Length fraction	4/25 in
Dimension - B Length inch	0.16 in
Dimension - Z inch	0.29 in
Dimension - Pad Width inch	0.31 in
Dimension - Hole Size fraction	8/47
Dimension - Bolt Size fraction	#6 - #8
Dimension - Hole Size inch	0.17 in
Dimension - Strip Length inch	3/16 in
Dimension - Stud Size inch	#6 - #8
Dimension - Length Overall inch	1 in
Dimension - D inch	0.02 in
Dimension - N inch	0.2 in

General

Insulation Type	Nylon
Color Code	Blue
Physical Attribute - Tongue Type	Flanged Fork
Trade Name	INSULUG™
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Shrouded
Insulation	Y
UPC 12 Digit	781810028711
UPC 14 Digit GTIN	00781810028711
Material	Copper
Plating Type	Electro Tin
UPC	781810028711

Logistics

Minimum Pack Quantity	2000
Packaging Type	Reel
Carton Quantity	10000

Operational

Temperature Rating	105° C
--------------------	--------

Product Assets

[Catalog \[English\]](#)