



# YAD10516, Uninsulated Ring Terminal For 12 - 10 AWG

By Burndy  
Catalog # [YAD10516](#)

Uninsulated Ring Terminal For 12 - 10 AWG



## Features

- Constructed of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Long brazed seam barrel and deep V groove inner serrations provide optimum conductivity reliability and holding power after crimping
- Electro-tin plating to provide durable, long-lasting corrosion resistance
- Wire range is clearly marked on terminal for easy identification
- Inspection hold for an easy visual check of wire insertion
- Long neck terminal permits easy bending and stacking of several terminals on a common stud

## Application

For control wiring and other standard duty applications

## Specifications

|                              |                      |
|------------------------------|----------------------|
| Buy American Compliant       | Contact Manufacturer |
| EU RoHS Indicator            | Yes                  |
| Certification - ETL          | No                   |
| Standards - RoHS Compliance  | CM                   |
| Status                       |                      |
| Certification - CSA Approved | Yes                  |
| UL Listed                    | Yes                  |

Buy America(n) Qualified      Contact Manufacturer

## Conductor

Conductor Size      12 - 10 AWG

## Configuration

Connector Type      Ring Terminal

## Dimensions

Dimension - Bolt Size fraction      5/16

## General

|            |              |
|------------|--------------|
| Sub Brand  | HYLUG        |
| Trade Name | HYLUG™       |
| Type       | Ring Tongue  |
| Material   | Copper       |
| UPC        | 781810806432 |

## Logistics

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 500   |
| Carton Quantity       | 500   |
| Pallet Quantity       | 99999 |

## Product Assets

[Catalog \[English\]](#)