

YAE10N110LFBOX, Nylon Locking Fork Terminal For 12 - 10 AWG

By Burndy

Catalog # [YAE10N110LFBOX](#)

Nylon Locking Fork Terminal For 12 - 10 AWG



Features

- Locking fork tongue design allows fast installation, screw only has to be loosened for termination
- Internal configuration of the fork prevents the terminal from coming off the screw without applying a pulling force
- Locking fork is made from a copper alloy and permits many installations while maintaining proper spring retention of forks

Application

Power Connector

Specifications

Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	12 - 10 AWG
Conductor - Copper Str Size Range	12 AWG - 10 AWG
Conductor Type	CU C Str-Size

Configuration

Connector Type	Locking Fork Terminal
----------------	-----------------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Z inch	0.29 in
Dimension - L Length Overall mm	26 mm
Dimension - Pad Width inch	0.30 in
Dimension - Bolt Size fraction	#4 - #6
Dimension - Strip Length inch	11/32
Dimension - Stud Size fraction	• #4 • #5 • #6
Dimension - Stud Size inch	#4 - #6
Dimension - Length Overall inch	1.02 in

General

Sub Brand	INSULUG
Insulation Type	Nylon
Physical Attribute - Tongue Type	Fork
Trade Name	INSULUG™
Plated	Y
Insulation	Y
Type	Long Barrel
UPC 12 Digit	781810524411
UPC 14 Digit GTIN	00781810524411
Material	Copper
Plating Type	Unplated
UPC	781810524411

Logistics

Minimum Pack Quantity	1
Carton Quantity	100
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)