



# Cu T-Type Battery Post Connector Terminal, 2 AWG, Negative

By Burndy  
Catalog # [YAEBAF2CNTN](#)



2 AWG NEGATIVE T-STYLE BATTERY POST TERMINAL

### Features

- Barrel is color coded for easy identification
- Chamfered end
- Made of copper alloy, tin plated for corrosion resistance and RoHS compliance
- Supplied standard with stainless steel hardware installed
- Clamp color coded by polarity - Red is Postive, Black is Negative
- Not UL Listed but tested and met UL486A-486B pullout requirements

### Application

Battery Post Terminal

### Specifications

|                               |     |
|-------------------------------|-----|
| Certification - ETL           | No  |
| Certification - UL Recognized | No  |
| Standards - RoHS Compliant    | Yes |
| Standards - RoHS Compliance   | CM  |
| Status                        |     |
| Certification - cULus         | No  |
| UL Listed                     | No  |
| Certification - CSA Approved  | No  |

### Conductor

|                                |           |
|--------------------------------|-----------|
| Conductor - Copper Flex G Size | 2 AWG     |
| Conductor - Copper Str         | 2 AWG     |
| Compact Size                   |           |
| Conductor - Copper DLO Size    | 2 AWG     |
| Conductor Size                 | 2 AWG     |
| Conductor - Copper Flex H Size | 2 AWG     |
| Conductor - Material           | COPPER    |
| Wire Size                      | 2 AWG     |
| Conductor - Copper Flex K Size | 2 AWG     |
| Conductor - Copper Flex M Size | 2 AWG     |
| Conductor Type                 | CODE/FLEX |
| Conductor - Copper Str Size    | 2 AWG     |
| Range                          |           |
| Conductor - Copper Str Size    | 2 AWG     |
| Conductor - Copper Flex I Size | 2 AWG     |

### Configuration

|                |                |
|----------------|----------------|
| Connector Type | BATTERY T-POST |
|----------------|----------------|

### Current

|                   |       |
|-------------------|-------|
| Voltage Rating    | 35 kV |
| Voltage - Maximum | 35000 |

### Dimensions

|                                   |           |
|-----------------------------------|-----------|
| Package Height                    | 1.050 in  |
| Physical Attribute - Tongue Angle | Straight  |
| Package Weight                    | 2.500 lb. |
| Package Length                    | 9.250 in  |
| Package Width                     | 4.600 in  |
| Dimension - L Length Overall      | 60 mm     |
| Dimension - Diameter Min Size     | 0.33 in   |
| Dimension - Diameter Max Size     | 0.57 in   |
| Dimension - Length Overall        | 2.36 in   |
| Dimension - Strip Length inch     | 1-9/32    |

### Force Related

|                     |           |
|---------------------|-----------|
| Installation Torque | 72 LBS/in |
| Recommended in-lb   |           |

### General

|                   |                |
|-------------------|----------------|
| Plated            | Y              |
| Color Code        | Brown          |
| Trade Name        | HYDENT™        |
| Die Index         | 10             |
| UPC               | 781810563816   |
| Type              | OEM Terminals  |
| Material          | COPPER         |
| Plating Type      | Tin Plated     |
| Finish Type       | Tin-Plated     |
| UPC 12 Digit      | 781810563816   |
| UPC 14 Digit GTIN | 00781810563816 |

### Logistics

|                 |      |
|-----------------|------|
| Pallet Quantity | 7200 |
| Carton Quantity | 100  |

### Operational

|                    |     |
|--------------------|-----|
| Temperature Rating | 194 |
|--------------------|-----|



A Hubbell brand