



YAE12N14, Nylon Ring Terminal For 14 - 12 AWG

By Burndy
Catalog # [YAE12N14](#)

Nylon Ring Terminal For 14 - 12 AWG

Features

- Multi-finger insulation grip provides superior insulation holding characteristics, especially on EPR and other elastic-type insulation
- Brazed seam for a strong, more durable termination
- Manufactured of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove, inner barrel serrations for optimum conductivity, reliability, and holding power
- Smooth funnel entry for easy wire insertion

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	• UL486 • Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	• UL486 • Military Specified (Mil-Spec)
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	14 - 12 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	14 AWG - 12 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Pad Width inch	0.25 in
Package Height	0.000 in
Dimension - Bolt Size fraction	#4 - #6
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.286 in
Dimension - Length Overall inch	1.023 in
Dimension - Strip Length inch	21/64 in
Dimension - Stud Size inch	#4 - #6

General

Feature - Barrel Type	Standard
Plated	Y
Color Code	Green
Insulation Type	Nylon
Trade Name	INSULUG™
Physical Attribute - Tongue Type	Ring Terminal
UPC	781810550502
Insulation	Y
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810550502
UPC 14 Digit GTIN	00781810550502

Logistics

Pallet Quantity	99999
Carton Quantity	500
Packaging Type	Bulk

Operational

Temperature Rating	105° C
--------------------	--------

Product Assets

[Catalog \[English\]](#)