



Straight Style Battery Post Terminal, 2 AWG, Positive

By Burndy

Catalog # [YAEBAS2CPTN](#)

2 AWG POSITIVE STRAIGHT STYLE BATTERY POST TERMINAL



Features

- Barrel is color coded for easy identification
- Chamfered end
- Made of copper alloy, tin plated for corrosion resistance and RoHS compliance
- Supplied standard with stainless steel hardware installed
- Clamp color coded by polarity - Red is Postive, Black is Negative
- Not UL Listed but tested and met UL486A-486B pullout requirements

Application

Battery Post Terminal

Specifications


Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Flex G Size	2 AWG
Conductor - Copper Str	2 AWG
Compact Size	
Conductor - Copper DLO Size	2 AWG
Conductor Size	2 AWG
Conductor - Copper Flex H Size	2 AWG
Conductor - Material	COPPER
Wire Size	2 AWG
Conductor - Copper Flex K Size	2 AWG
Conductor - Copper Flex M Size	2 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size	2 AWG
Range	
Conductor - Copper Str Size	2 AWG
Conductor - Copper Flex I Size	2 AWG

Configuration

Connector Type	BATTERY STRAIGHT POST
----------------	-----------------------



Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	1.000 in
Physical Attribute - Tongue Angle	Straight
Package Weight	1.270 lb.
Package Length	7.900 in
Package Width	3.400 in
Dimension - L Length Overall	59 mm
Dimension - Length Overall	2.30 in
inch	
Dimension - Strip Length inch	1-3/32 in

Force Related

Installation Torque	72 LBS/in
Recommended in-lb	

General

Color Code	Brown
Trade Name	HYLUG™
Die Index	10
UPC	781810562567
Type	OEM Terminals
Material	Copper
Plating Type	Tin Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810562567
UPC 14 Digit GTIN	00781810562567

Logistics

Minimum Pack Quantity	10
Pallet Quantity	13000
Carton Quantity	100

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)