

YAE14N65, Nylon Ring Terminal For 16 - 14 AWG

By Burndy
Catalog # [YAE14N65](#)

Nylon Ring Terminal For 16 - 14 AWG



Features

- Multi-finger insulation grip provides superior insulation holding characteristics, especially on EPR and other elastic-type insulation
- Brazed seam for a strong, more durable termination
- Manufactured of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove, inner barrel serrations for optimum conductivity, reliability, and holding power
- Smooth funnel entry for easy wire insertion

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Industry Standard(s)	• UL486 • Military Specified (Mil-Spec)
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor Size	16 - 14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Z inch	0.281 in
Dimension - Pad Width inch	0.31 in
Package Height	0.000 in
Dimension - Bolt Size fraction	3/8
Dimension - Hole Size inch	0.20 in
Dimension - Strip Length inch	3/16 in
Dimension - Stud Size inch	3/8 in
Dimension - Length Overall	0.91 in

General

Insulation Type	Nylon
Color Code	Blue
Physical Attribute - Tongue Type	Ring Terminal
Trade Name	INSULUG™
Plated	Y
Feature - Barrel Type	Standard
Insulation	Y
UPC 12 Digit	781810542712
UPC 14 Digit GTIN	00781810542712
Material	Copper
Plating Type	Tin
UPC	781810542712

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000
Pallet Quantity	99999

Operational

Temperature Rating	105° C
--------------------	--------

Product Assets

[Catalog \[English\]](#)