




YAE14N76F, Nylon Fork Terminal For 16 - 14 AWG

By Burndy

Catalog # [YAE14N76F](#)

Nylon Fork Terminal For 16 - 14 AWG



Features

- Multi-finger insulation grip provides superior insulation holding characteristics, especially on EPR and other elastic-type insulations
- Brazed seam provides a stronger, more durable termination
- Manufactured of pure electrolytic copper for maximum conductivity, low resistance, and ductility for excellent crimp forming properties
- Deep V groove, inner barrel serrations for optimum conductivity, reliability and holding power
- Smooth funnen entry for easy wire insertion

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Industry Standard(s)	• UL486 • Military Specified (Mil-Spec)
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Aircraft Size Range	AN16 - AN14
Conductor Size	16 - 14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Fork Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
----------------	----------



A Hubbell brand

Package Width	0.000 in
Dimension - B Length fraction	4/25 in
Package Weight	0.000 lb.
Dimension - B Length inch	0.16 in
Dimension - Z inch	0.25 in
Dimension - Pad Width inch	0.28 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/20
Dimension - Bolt Size fraction	#4 - #6
Dimension - Hole Size inch	0.15 in
Dimension - Strip Length inch	3/16 in
Dimension - Stud Size inch	#4 - #6
Dimension - Length Overall inch	0.85 in
Dimension - N inch	0.11 in

General

Insulation Type	Nylon
Color Code	Blue
Physical Attribute - Tongue Type	Fork Terminal
Trade Name	INSULUG™
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Shrouded
Insulation	Y
UPC 12 Digit	781810804568
UPC 14 Digit GTIN	00781810804568
Material	Copper
Plating Type	Electro Tin
UPC	781810804568

Logistics

Minimum Pack Quantity	1000
Packaging Type	Bulk
Carton Quantity	1000
Pallet Quantity	99999

Operational

Temperature Rating	105° C
--------------------	--------

Product Assets

[Catalog \[English\]](#)