

YAE18N104LFBOX, Nylon Locking Fork Terminal For 22 - 18 AWG

By Burndy
Catalog # [YAE18N104LFBOX](#)



Nylon Locking Fork Terminal For 22 - 18 AWG

Features

- Locking fork tongue design allows fast installation, screw only has to be loosened for termination
- Internal configuration of the fork prevents the terminal from coming off the screw without applying a pulling force
- Locking fork is made from a copper alloy and permits many installations while maintaining proper spring retention of forks

Application

Power Connector

Specifications

Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	22 - 18 AWG
Conductor - Copper Str Size Range	22 AWG - 18 AWG
Conductor Type	CU C Str-Size

Configuration

Connector Type	Locking Fork Terminal
----------------	-----------------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Z inch	0.32 in

Dimension - L Length Overall mm	24 mm
Dimension - Pad Width inch	0.25 in
Package Height	0.000 in
Dimension - Bolt Size fraction	#4 - #6
Dimension - Strip Length inch	7/32 in
Dimension - Stud Size fraction	• #4 • #5 • #6
Dimension - Stud Size inch	#4 - #6
Dimension - Length Overall inch	0.95 in

General

Sub Brand	INSULUG
Insulation Type	Nylon
Color Code	Red
Physical Attribute - Tongue Type	Locking Fork
Trade Name	INSULUG™
Plated	Y
Feature - Barrel Type	Standard
Insulation	Y
Type	Long Barrel
UPC 12 Digit	781810524589
UPC 14 Digit GTIN	00781810524589
Material	Copper
Plating Type	Unplated
UPC	781810524589

Logistics

Minimum Pack Quantity	100
Carton Quantity	100
Pallet Quantity	1

Operational

Temperature Rating	105° C
--------------------	--------

Product Assets

[Catalog \[English\]](#)