

YAES10N11F, Nylon Fork Terminal For 12 - 10 AWG

By Burndy
Catalog # [YAES10N11F](#)

Nylon Fork Terminal For 12 - 10 AWG



Features

- Fork tongue design for faster installation
- Screw needs only to be loosened (not completely removed) for termination

Application

Power Connector

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	- UL486 - Military Specified (Mil-Spec)
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Size	12 AWG 10 AWG
Conductor Size	12 - 10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Fork Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Outside Diameter inch	0.32 in
Dimension - Pad Width inch	0.28 in
Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - Strip Length inch	11/32 in
Dimension - Z inch	0.26 in
Dimension - Bolt Size fraction	#4 - #6
Dimension - Inside Diameter inch	0.22 in
Dimension - Length Overall inch	0.95 in
Dimension - N inch	0.14 in

General

Insulation Type	Nylon
Trade Name	INSULUG™
Insulation	Y
Sub Brand	INSULUG
Color Code	Yellow
Physical Attribute - Tongue Type	Fork
Plated	Y
Feature - Barrel Style	Shrouded
Type	YAES-F
UPC 12 Digit	781810805022
UPC 14 Digit GTIN	00781810805022
Material	Copper
Plating Type	Tin
UPC	781810805022

Logistics

Minimum Pack Quantity	500
Carton Quantity	500
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)