

YAE18N60F, Nylon Fork Terminal For 22 - 18 AWG

By Burndy

Catalog # [YAE18N60F](#)

Nylon Fork Terminal For 22 - 18 AWG



Features

- Multi-finger insulation grip provides superior insulation holding characteristics, especially on EPR and other elastic-type insulations
- Brazed seam provides a stronger, more durable termination
- Manufactured of pure electrolytic copper for maximum conductivity, low resistance, and ductility for excellent crimp forming properties
- Deep V groove, inner barrel serrations for optimum conductivity, reliability and holding power
- Smooth funnel entry for easy wire insertion

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	• UL486 • Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
Industry Standard(s)	• UL486 • Military Specified (Mil-Spec)
Certification - CSA Approved	No
UL Listed	Yes

Conductor

Conductor - Copper Str Aircraft Size	• AN 22 • AN 20 • AN 18 • AN 16
Conductor Size	22 - 18 AWG
Conductor - Copper Str Size	• 20 AWG • 18 AWG • 16 AWG
Conductor - Copper Str Size Range	20 AWG - 16 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Fork Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length fraction	4/25 in
Package Weight	0.000 lb.
Dimension - B Length inch	0.16 in
Dimension - Z inch	0.24 in
Dimension - Pad Width inch	0.21 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/25
Dimension - Bolt Size fraction	#4
Dimension - Hole Size inch	0.12 in
Dimension - Strip Length inch	3/16 in
Dimension - Stud Size inch	#4
Dimension - Length Overall inch	0.92 in
Dimension - N inch	0.19 in

General

Insulation Type	Nylon
Color Code	Red
Physical Attribute - Tongue Type	Fork
Trade Name	INSULUG™
Plated	Y
Insulation	Y
UPC 12 Digit	781810034750
UPC 14 Digit GTIN	00781810034750
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810034750

Logistics

Minimum Pack Quantity	1000
Packaging Type	Bulk
Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)