



YAE22G13BOX, Nylon Ring Terminal For 26 - 20 AWG

By Burndy

Catalog # [YAE22G13BOX](#)

Nylon Ring Terminal For 26 - 20 AWG



Features

- Multi-finger insulation grip provides superior insulation holding characteristics, especially on EPR and other elastic-type insulation
- Brazed seam for a strong, more durable termination
- Manufactured of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove, inner barrel serrations for optimum conductivity, reliability, and holding power
- Smooth funnel entry for easy wire insertion

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Industry Standard(s)	Military Specified (Mil-Spec)
Certification - ETL	No
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Str Aircraft Size	• AN 26 • AN 22 • AN 20
Conductor Size	26 - 20 AWG
Conductor Type	• CU C Str-Size • CU C Solid-Size
Conductor Range	#26 AWG to #20 AWG

Configuration


Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Current

Voltage - Maximum	300 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in



A Hubbell brand

Package Weight	0.000 lb.
Dimension - L Length Overall mm	19 mm
Dimension - Pad Width inch	0.25 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - Strip Length inch	5/32
Dimension - Stud Size inch	• #4 • #5 • #6
Dimension - Z inch	0.22 in
Dimension - Bolt Size fraction	#4 - #6
Cable Insulation Diameter Maximum	0.098 in
Dimension - Length Overall inch	0.74 in
Dimension - N inch	0.13 in

General

Insulation Type	Nylon
Trade Name	INSULUG™
Insulation	Y
Military Specification	MS25036
Color Code	Amber
Physical Attribute - Tongue Type	Ring
Plated	Y
UPC 12 Digit	781810023266
UPC 14 Digit GTIN	00781810023266
Material	Copper
Plating Type	Tin
UPC	781810023266

Logistics

Minimum Pack Quantity	100
Carton Quantity	1200
Pallet Quantity	99999

Operational

Temperature Rating	105°C
--------------------	-------

Product Assets

[Catalog \[English\]](#)