



YAEV2CL3BOX, Nylon Ring Terminal For 2 AWG

By Burndy
Catalog # [YAEV2CL3BOX](#)

Nylon Ring Terminal For 2 AWG



Features

- Double thick tongue for maximum reliability and electrical capacity plus an extra strong terminal tongue
- Manufactured from one-piece pure electrolytic copper — high conductivity, low resistance with no seams to split plus ductility for excellent crimp forming properties
- Electro-tin plated to provide long-lasting corrosion resistance
- Nylon insulation is locked in place — Insulation will not move or twist off
- 600 volt nylon insulation providing high dielectric strength and stability in demanding oily environmental conditions
- Color Coded providing quick, easy wire size connector selection

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Industry Standard(s)	• UL486 • Military Specified (Mil-Spec)
Certification - CSA Approved	No
UL Listed	Yes

Conductor

Conductor - Copper Str Aircraft Size Range	AN 2
Conductor Size	2 AWG
Conductor - Copper Str Size	2AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Connector Type Ring Terminal

Current

Voltage - Maximum 600 V

Dimensions

Dimension - B Length inch	0.56
Dimension - L Length Overall mm	51
Dimension - Bolt Size fraction	#10
Dimension - Stud Size inch	#10
Dimension - Length Overall inch	2.02

General

Insulation Type	Nylon
Color Code	Red
Physical Attribute - Tongue Type	Ring
Trade Name	INSULUG™
Plated	Y
Insulation	Y
UPC 12 Digit	781810532959
UPC 14 Digit GTIN	00781810532959
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810532959

Logistics

Minimum Pack Quantity	50
Carton Quantity	50
Pallet Quantity	44550

Product Assets

[Catalog \[English\]](#)