

YAEV4CLBOX, Nylon Ring Terminal For 4 AWG

By Burndy
Catalog # [YAEV4CLBOX](#)



Nylon Ring Terminal For 4 AWG

Features

- Double thick tongue for maximum reliability and electrical capacity plus an extra strong terminal tongue
- Manufactured from one-piece pure electrolytic copper — high conductivity, low resistance with no seams to split plus ductility for excellent crimp forming properties
- Electro-tin plated to provide long-lasting corrosion resistance
- Nylon insulation is locked in place — Insulation will not move or twist off
- 600 volt nylon insulation providing high dielectric strength and stability in demanding oily environmental conditions
- Color Coded providing quick, easy wire size connector selection

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Industry Standard(s)	• UL486 • Military Specified (Mil-Spec)
Certification - CSA Approved	No
UL Listed	Yes

Conductor

Conductor - Copper Str Aircraft Size Range	AN 4
Conductor Size	4 AWG
Conductor - Copper Str Size	4AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Connector Type	Ring Terminal
----------------	---------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - B Length inch	0.43
Dimension - L Length Overall mm	41
Package Height	0.000 in
Dimension - Bolt Size fraction	1/4
Dimension - Stud Size inch	1/4
Dimension - Length Overall inch	1.62

General

Die Index	437
Insulation Type	Nylon
Color Code	Yellow
Physical Attribute - Tongue Type	Ring
Trade Name	INSULUG™
Plated	Y
Insulation	Y
UPC 12 Digit	781810532911
UPC 14 Digit GTIN	00781810532911
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810532911

Logistics

Minimum Pack Quantity	50
Carton Quantity	50
Pallet Quantity	44550

Product Assets

[Catalog \[English\]](#)