



Straight Style Battery Post Term, 2/0 AWG, Negative, Bulk

By Burndy

Catalog # [YAEBAS26NTNOEM](#)

2/0 AWG NEGATIVE STRAIGHT STYLE BATTERY POST
TERMINAL



Features

- Barrel is color coded for easy identification
- Chamfered end
- Made of copper alloy, tin plated for corrosion resistance and RoHS compliance
- Supplied standard with stainless steel hardware installed
- Clamp color coded by polarity - Red is Postive, Black is Negative
- Not UL Listed but tested and met UL486A-486B pullout requirements

Application

Battery Post Terminal

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliant	Yes
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Flex G Size	2/0 AWG
Conductor - Copper Str	2/0 AWG
Compact Size	
Conductor - Copper DLO Size	2/0 AWG
Conductor Size	2/0 AWG
Conductor - Copper Flex H Size	2/0 AWG
Conductor - Material	COPPER
Wire Size	2/0 AWG
Conductor - Copper Flex K Size	2/0 AWG
Conductor - Copper Flex M Size	2/0 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size	2/0 AWG
Range	
Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Flex I Size	2/0 AWG

Configuration

Connector Type	BATTERY STRAIGHT POST
----------------	-----------------------

Current



A Hubbell brand

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Physical Attribute - Tongue Angle	Straight
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	60 mm
mm	
Dimension - Outside Diameter	0.68 in
inch	
Dimension - Inside Diameter	0.502 in
inch	
Dimension - Length Overall	2.36 in
inch	

Force Related

Installation Torque	72 LBS/in
Recommended in-lb	

General

Color Code	Black
Trade Name	HYLUG™
Die Index	13
UPC	781810547564
Type	OEM Terminals
Material	Copper
Plating Type	Tin Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810547564
UPC 14 Digit GTIN	00781810547564

Logistics

Minimum Pack Quantity	200
Pallet Quantity	1
Carton Quantity	1

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)