



YAEV8CL1BOX, Nylon Ring, 8 AWG, 1/4" Stud

By Burndy

Catalog # [YAEV8CL1BOX](#)

Nylon Ring Terminal For 8 AWG, 1/4" Stud, Double thick tongue for maximum reliability and electrical capacity



Features

- Double thick tongue for maximum reliability and electrical capacity plus an extra strong terminal tongue
- Manufactured from one-piece pure electrolytic copper — high conductivity, low resistance with no seams to split plus ductility for excellent crimp forming properties
- Electro-tin plated to provide long-lasting corrosion resistance
- Nylon insulation is locked in place — Insulation will not move or twist off
- 600 volt nylon insulation providing high dielectric strength and stability in demanding oily environmental conditions
- Color Coded providing quick, easy wire size connector selection

Application

For Very Demanding High Vibration Applications Encountered In Aircraft And Aboard Ships As Well As Motor Lead Applications In Hospitals, Industrials And Generating Plants

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	• UL486 • Military Specified (Mil-Spec)
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	8 AWG
Conductor Size	8 AWG
Conductor - Copper Str Aircraft Size	AN 8
Conductor Type	• CU C Str Aircraft-Size • CU C Str-Size
Conductor - Copper Str Size Range	8 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Pad Width inch	0.46 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - P inch	0.13 in
Dimension - L Length Overall mm	37 mm
Dimension - Strip Length inch	7/16
Dimension - Stud Size inch	1/4
Dimension - Bolt Size fraction	1/4
Dimension - B Length fraction	9/25 in
Dimension - Z inch	0.32 in
Dimension - B Length inch	0.36 in
Dimension - N inch	0.23 in
Dimension - Length Overall inch	1.47 in

General

Product Family	COMPRESSION
Insulation Type	Nylon
Trade Name	INSULUG™
Die Index	435
Insulation	Y
Military Specification	MS25036
Plated	Yes
Color Code	Red
Physical Attribute - Tongue Type	Ring
Sub Brand	INSULUG
Product Type	Terminal
UPC	781810023303
Type	YAEV-L, Heavy Duty
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810023303
UPC 14 Digit GTIN	00781810023303

Logistics

Minimum Pack Quantity	1
Carton Quantity	50

Operational

Temperature Rating	105°C
--------------------	-------



A Hubbell brand