



YAGB4CLTC12FX, Battery Terminal, 4 AWG, 1-Hold, 1/4" Stud

By Burndy
Catalog # [YAGB4CLTC12FX](#)

4 AWG, 1/4 Stud Size, One Hole Cu Battery Terminal



Features

- Color coded for easy identification
- Chamfered end
- Made of copper alloy, tin plated for corrosion resistance and RoHS compliance
- Not UL Listed but tested and met UL486A-486B pullout requirements

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Flex G Size	4 AWG
Conductor - Copper DLO Size Range	4 AWG
Conductor - Copper DLO Size	4 AWG
Conductor Size	4 AWG
Conductor - Copper Flex H Size	4 AWG
Conductor - Copper Flex G Size Range	4 AWG
Conductor - Material	COPPER
Wire Size	4 AWG
Conductor - Copper Flex K Size Range	4 AWG
Conductor - Copper Flex K Size	4 AWG
Conductor - Copper Flex M Size	4 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	4 AWG
Conductor - Copper Str Size	4 AWG
Conductor - Copper Flex H Size Range	4 AWG
Conductor - Copper Flex I Size	4 AWG
Conductor - Copper Flex I Size Range	4 AWG

Configuration

Connector Type	GROUNDING/STARTER LUGS
----------------	------------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	1.800 in
Dimension - Hole Size fraction	1/2
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Package Weight	0.800 lb.
Package Length	3.450 in
Package Width	2.550 in
Dimension - L Length Overall mm	50 mm
Dimension - Hole Size mm	13.5 mm
Dimension - Bolt Size inch	0.5
Dimension - Hole Size inch	0.53
Dimension - Length Overall inch	1.97 in
Dimension - Strip Length inch	15/16 in
Dimension - Stud Size fraction	1/2

General

Color Code	Gray
Trade Name	HYLUG™
Die Index	6
UPC	781810562765
Type	OEM Terminals
Material	COPPER
Finish Type	Tin-Plated
UPC 12 Digit	781810562765
UPC 14 Digit GTIN	00781810562765

Logistics

Pallet Quantity	42000
Carton Quantity	200

Operational

Temperature Rating	194
--------------------	-----



A Hubbell brand