



YAK311A2G2, Aluminum - Compression Stacking Terminal (HYLUG Terminal)

By Burndy
Catalog # [YAK311A2G2](#)



Aluminum Stacking compression terminal, 397.5 Kcmil, 7.75 IN L,
Up to eight conductors can be stacked on one 4 hole pad

Features

- Aluminum Stacking compression terminal
- 397.5 kcmil
- Up to eight conductors can be stacked on one 4 hole pad

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	397.5 kcmil
Conductor - AL Str Size Range	397.5 kcmil
Conductor - Copper Str Size Range	397.5 kcmil
Conductor - Copper Str Size	397.5 kcmil

Configuration

Physical Attribute - Number of Crimps Required	2
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.62 in
Dimension - Bolt Hole Size inch	0.50 in
Package Height	0.000 in
Physical Attribute - Tongue Angle	Straight
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	197 mm
Dimension - B Length inch	2.41 in
Dimension - Outside Diameter inch	1.25 in
Dimension - D inch	3.06 in
Dimension - N inch	0.62 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	7.75 in
Dimension - Strip Length inch	2-1/2 in

General

Feature - Barrel Style	Chamfered
Plated	N
Trade Name	HYLUG™
Physical Attribute - Tongue Type	Standard
Die Index	317 705
UPC	781810187159
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810187159
UPC 14 Digit GTIN	00781810187159

Logistics

Minimum Pack Quantity	4
Pallet Quantity	1400
Carton Quantity	8

Product Assets

[Catalog \[English\]](#)