



YAL4C2T14, Compression Terminal

By Burndy

Catalog # [YAL4C2T14](#)

Copper Compression Terminal



Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper DLO Size Range	N/A
Conductor Size	4 AWG
Conductor - Copper Solid Size	4 AWG
Conductor - Copper Solid Size Range	4 AWG
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Size Range	4 AWG
Conductor - Copper Str Size	4 AWG

Configuration

Physical Attribute - Number of Holes	2
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.56 in
Dimension - Bolt Hole Size inch	0.27 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/4
Dimension - Bolt Size fraction	1/4
Physical Attribute - Tongue	Straight

Angle



A Hubbell brand

Dimension - B Length fraction	3/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.32 in
Dimension - L Length Overall mm	56 mm
Dimension - B Length inch	0.73 in
Dimension - Outside Diameter inch	0.34 in
Dimension - D inch	1.20 in
Dimension - N inch	0.25 in
Dimension - Hole Size mm	6.9 mm
Dimension - Bolt Size inch	0.25
Dimension - Hole Size inch	0.27
Dimension - Length Overall inch	2.21 in
Dimension - Stud Size inch	1/4
Dimension - Stud Size fraction	1/4

General

Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Gray
Trade Name	HYLUG™
Physical Attribute - Tongue Type	Standard
Die Index	8
UPC	781810417492
Type	Standard Barrel, Tin Plated
Material	COPPER
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 14 Digit GTIN	00781810417492

Logistics

Carton Quantity	50
-----------------	----

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)