



YAES14K6NK, Radiation Resistant Insulated Ring Terminal For 16 - 14 AWG (Nickel Plated)

By Burndy
Catalog # [YAES14K6NK](#)

Radiation Resistant Insulated Ring Terminal For 16 - 14 AWG (Nickel Plated)

Features

- Insulation provides 200 megarad radiation resistance plus successfully tested for insulation compatibility
- An integral one-piece copper barrel/insulation grip and wire strain relief design provides improved physical strength characteristics over a multi-piece design
- The insulation is locked in place and will not move or twist off, thereby maintains proper dielectric values
- Manufactured from pure electrolytic copper to provide maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Bright tin-plated per MIL-T-10727 for durable long-lasting resistance to corrosion
- Deep inner barrel serrations provides excellent electrical conductivity and tensile strength values
- Brazed seam gives a stronger barrel design to minimize any possible splitting and eliminates folding
- Smooth funnel entry for easy wire insertion
- Color coded terminals provides easy wire size identification and inspection
- Coded raised dots in the die area of the connection after compression for visual identification that the correct tool and die were used for proper installation
- Inspection hole gives an additional visual check to ensure proper wire insertion
- Ring tongue design provides a secure termination under screw head that cannot be removed without the complete removal of the screw
- Multiple terminals may be stacked on a common stud easily providing flexibility and versatility

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	IEEE 323
Standards - RoHS Compliance Status	CM
Industry Standard(s)	IEEE 323
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Solid Size • 16 AWG



	• 15 AWG
	• 14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor Size	16 - 14 AWG
Conductor - Copper Str Size	• 16 AWG
	• 14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Type	• CU C Str-Size
	• CU C Solid-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Z inch	0.22 in
Dimension - L Length Overall mm	20 mm
Dimension - Pad Width inch	0.25 in
Dimension - Hole Size fraction	3/20
Dimension - Bolt Size fraction	#6
Dimension - Hole Size inch	0.15 in
Dimension - Strip Length inch	7/32 in
Dimension - Stud Size inch	#6
Dimension - Length Overall inch	0.77 in

General

Insulation Type	Radiation Resistant
Color Code	Blue
Physical Attribute - Tongue Type	Ring
Trade Name	INSULUG™
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Belled
Insulation	Y

Type	Radiation Resistant KYNAR	Logistics	
UPC 12 Digit	Ring Tongue	Minimum Pack Quantity	1000
UPC 14 Digit GTIN	781810211700	Carton Quantity	1000
Material	00781810211700	Pallet Quantity	99999
Plating Type	Copper		
UPC	Nickel	Product Assets	
	781810211700	Catalog [English]	

