

YAES14N53F, Nylon Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # [YAES14N53F](#)

Nylon Fork Terminal For 16 - 14 AWG



Features

- Fork tongue design for faster installation
- Screw needs only to be loosened (not completely removed) for termination

Application

Power Connector

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	- UL486 - Military Specified (Mil-Spec)
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Size	16 AWG 14 AWG
Conductor - Copper Solid Size	16 AWG 15 AWG 14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor Size	16 - 14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Fork Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Pad Width inch	0.31 in
Package Height	0.000 in
Dimension - Hole Size fraction	8/47
Dimension - Hole Size inch	0.17 in
Dimension - Strip Length inch	7/32 in
Dimension - Stud Size inch	#6 #8
Dimension - Z inch	0.26 in
Dimension - Bolt Size fraction	#6 - #8
Dimension - Length Overall inch	0.84 in
Dimension - N inch	0.17 in

General

Insulation Type	Nylon
Trade Name	INSULUG™
Insulation	Y
Sub Brand	INSULUG
Color Code	Blue
Physical Attribute - Tongue Type	Fork
Plated	Y
Feature - Barrel Type	Standard
Type	YAES-F
UPC 12 Digit	781810804810
UPC 14 Digit GTIN	00781810804810
Material	Copper
Plating Type	Tin
UPC	781810804810

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)