



YAES14N6F, Nylon Fork Terminal For 16 - 14 AWG

By Burndy

Catalog # [YAES14N6F](#)

Nylon Fork Terminal For 16 - 14 AWG



Features

- Fork tongue design for faster installation
- Screw needs only to be loosened (not completely removed) for termination

Application

Power Connector

Specifications

Buy American Compliant Certification - cULus	Contact Manufacturer
EU RoHS Indicator	No
Certification - UL Recognized	Yes
Industry Standard(s)	No
	• UL486
	• Military Specified (Mil-Spec)
Buy America(n) Qualified Certification - ETL	Contact Manufacturer
Standards - Industry Standards Met	No
Standards - RoHS Compliance Status	UL486
Certification - CSA Approved	CM
UL Listed	Yes
	Yes


Conductor

Conductor - Copper Str Size	• 16 AWG
	• 14 AWG
Conductor - Copper Solid Size	• 16 AWG
	• 15 AWG
	• 14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor Size	16 - 14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Fork Terminal

Current



Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Pad Width inch	0.28 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - Strip Length inch	7/32 in
Dimension - Stud Size inch	• #4
	• #5
	• #6
Dimension - Z inch	0.24 in
Dimension - Bolt Size fraction	#4 - #6
Dimension - Length Overall inch	0.79 in
Dimension - N inch	0.14 in

General

Insulation Type	Nylon
Trade Name	INSULUG™
Insulation	Y
Sub Brand	INSULUG
Color Code	Blue
Physical Attribute - Tongue Type	Fork
Plated	Y
Feature - Barrel Type	Standard
Type	YAES-F
UPC 12 Digit	781810805138
UPC 14 Digit GTIN	00781810805138
Material	Copper
Plating Type	Tin
UPC	781810805138

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)