



YAES18N50F, Nylon Fork Terminal For 22 - 18 AWG

By Burndy
Catalog # [YAES18N50F](#)



Nylon Fork Terminal For 22 - 18 AWG

Features

- Fork tongue design for faster installation
- Screw needs only to be loosened (not completely removed) for termination

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Industry Standard(s)	- UL486 - Military Specified (Mil-Spec)
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor Size	22 - 18 AWG
Conductor - Copper Str Size	22 AWG 20 AWG 18 AWG
Conductor - Copper Str Size Range	22 AWG - 18 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Fork Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Outside Diameter inch	0.24 in
Dimension - Pad Width inch	0.47 in
Dimension - Hole Size fraction	10/37
Dimension - Bolt Size fraction	1/4
Dimension - Hole Size inch	0.27 in
Dimension - Stud Size inch	1/4
Dimension - Length Overall inch	1.03 in
Dimension - N inch	0.24 in

General

Insulation Type	Nylon
Color Code	Red
Physical Attribute - Tongue Type	Fork
Trade Name	INSULUG™
Plated	Y
Feature - Barrel Type	Standard
Insulation	Y
UPC 12 Digit	781810027196
UPC 14 Digit GTIN	00781810027196
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810027196

Logistics

Minimum Pack Quantity	1000
Packaging Type	Bulk
Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)