



YALB120FM14, Compression Terminal

By Burndy
Catalog # [YALB120FM14](#)

Copper Compression Terminal

Features

- No inspection window is ideal for more corrosive environments as the barrel transition is not open
- Barrel is designed with internal chamfer at wire entry ensuring smooth insertion of the wire, preventing possible damaging of the wire strands
- Electro-tin plated unless specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with stamping
- Compatible Standards: IEC61238-1, UL 486A-486B, CSA-C22.2 No. 65-03

Application

Metric Wire Termination

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No

Conductor

Conductor Size	120 mm2
Conductor - Material	COPPER
Conductor Type	CLASS 5
Conductor - Copper Str Size	120 mm2

Configuration

Number of Pad Holes	1
Connector Type	METRIC

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.14 in
Dimension - Hole Size fraction	1/2
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	0.57 in
Dimension - L Length Overall mm	84.5 mm
Dimension - B Length inch	1.62 in
Dimension - Hole Size mm	14 mm
Dimension - Bolt Size inch	0.5
Dimension - Hole Size inch	0.56
Dimension - Length Overall inch	3.33 in
Dimension - Strip Length inch	1.69 in
Dimension - Stud Size fraction	1/2

General

Plated	Yes
Trade Name	HYLUG™
Die Index	15
UPC	781810641743
Type	Metric Terminals
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810641743
UPC 14 Digit GTIN	00781810641743

Logistics

Minimum Pack Quantity	10
-----------------------	----

Product Assets

[Catalog \[English\]](#)