



YAEV6CL, Nylon Ring Terminal, 6 AWG, 1/4" Stud

By Burndy
Catalog # [YAEV6CL](#)



Nylon Ring Terminal For 6 AWG, 1/4" Stud, Double thick tongue for maximum reliability and electrical capacity

Features

- Double thick tongue for maximum reliability and electrical capacity plus an extra strong terminal tongue
- Manufactured from one-piece pure electrolytic copper — high conductivity, low resistance with no seams to split plus ductility for excellent crimp forming properties
- Electro-tin plated to provide long-lasting corrosion resistance
- Nylon insulation is locked in place — Insulation will not move or twist off
- 600 volt nylon insulation providing high dielectric strength and stability in demanding oily environmental conditions
- Color Coded providing quick, easy wire size connector selection

Application

For Very Demanding High Vibration Applications Encountered In Aircraft And Aboard Ships As Well As Motor Lead Applications In Hospitals, Industrials And Generating Plants

Specifications

Standards - Industry Standards Met	• UL486 • Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
Industry Standard(s)	• UL486 • Military Specified (Mil-Spec)
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Size	6 AWG
Conductor - Copper Str Aircraft Size Range	AN 6
Conductor - Copper Str Aircraft Size	AN 6
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor - Copper Str Size	6

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Pad Width inch	0.48 in
Package Height	0.000 in
Dimension - Bolt Size fraction	1/4
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.29 in
Dimension - P inch	0.13 in
Dimension - B Length inch	0.42 in
Dimension - N inch	0.24 in
Dimension - Length Overall inch	1.56 in
Dimension - Stud Size inch	1/4

General

Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Yes
Color Code	Blue
Product Family	COMPRESSION
Insulation Type	Nylon
Trade Name	INSULUG™
Physical Attribute - Tongue Type	Ring
Sub Brand	INSULUG
Die Index	436
Product Type	Terminal
UPC	781810027707
Type	YAEV-L, Heavy Duty
Insulation	Y
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810027707
UPC 14 Digit GTIN	00781810027707

Logistics

Pallet Quantity	800
Carton Quantity	400

Product Assets

[Catalog \[English\]](#)



A Hubbell brand