



YAG8CLTC12FX, Compression Terminal, 8 Flex G,H,I,K,M, DLO, 8 AWG, Cu, 1-Hole, 1/2" Stud, Standard Barrel

By Burndy
Catalog # [YAG8CLTC12FX](#)

8 Flex G,H,I,K,M,DLO, 8 AWG CU, One Hole, 1/2 Stud Size, Standard Barrel Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Red Color Code, 49 Die Index.

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- For applications greater than 2000 Volts consult cable manufacturer for voltage stress relief instruction

Application

Wire Termination

General

Catalog Number	YAG8CLTC12FX
Color Code	Red
Connector Type	STANDARD BARREL
Die Index	49
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	621945518223
UPC 14 Digit GTIN	000

Dimensions

Dimension - B Length fraction	7/16 in
Dimension - B Length inch	0.44 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Height mm	0 mm



Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.53
Dimension - Hole Size mm	13.5 mm
Dimension - L Length Overall mm	45 mm
Dimension - Length Overall inch	1.76 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	0.27 in
Dimension - Pad Width inch	0.71 in
Dimension - Strip Length inch	1/2
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2
Dimension - Z (inch)	0.55 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	8 AWG
Conductor - Copper DLO Size Range	8 AWG
Conductor - Copper Flex G Size	"8 AWG"
Conductor - Copper Flex G Size Range	8 AWG
Conductor - Copper Flex H Size	"8 AWG"
Conductor - Copper Flex H Size Range	8 AWG
Conductor - Copper Flex I Size	"8 AWG"
Conductor - Copper Flex I Size Range	8 AWG
Conductor - Copper Flex K Size	"8 AWG"
Conductor - Copper Flex K Size Range	8 AWG
Conductor - Copper Flex M Size	"8 AWG"

Conductor - Copper Solid Size Range	8-6 Sol
Conductor - Copper Str Compact Size	"8 AWG"
Conductor - Copper Str Navy Size	23
Conductor - Copper Str Size	"8 AWG"
Conductor - Copper Str Size Range	8 AWG
Conductor - CopperWeld C Solid Size	8 AWG
Conductor - CopperWeld Str Size	8 A AWG;8 C AWG;8 D AWG
Conductor - Material	COPPER
Conductor Size	8 AWG
Conductor Type	CODE/FLEX
Wire Size	8 AWG

Certifications And Compliance

Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM

UL Listed	Yes
-----------	-----

Logistics

Carton Quantity	50
Minimum Pack Quantity	50000

Product Assets

- [Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Medium & Large HYDENT Copper & Aluminum Terminal Crimp Instructions with 750 Series 12-Ton Tool](#)
- [Installation Manuals - Copper Flex Standard Terminals Tooling and Installation Instructions](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50000268](#)
- [Specifications - YAG8CLTC12FX](#)
- [Video - HYDENT Compression Terminal Overview Video](#)

