



YALB16M8, Compression Terminal

By Burndy
Catalog # [YALB16M8](#)

Copper Compression Terminal



Features

- No inspection window is ideal for more corrosive environments as the barrel transition is not open
- Barrel is designed with internal chamfer at wire entry ensuring smooth insertion of the wire, preventing possible damaging of the wire strands
- Electro-tin plated unless specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with stamping
- Compatible Standards: IEC61238-1, UL 486A-486B, CSA-C22.2 No. 65-03

Application

Metric Wire Termination

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No

Conductor

Conductor Size	16 mm2
Conductor - Material	COPPER
Conductor Type	CLASS 2
Conductor - Copper Str Size	16 mm2

Configuration

Connector Type	METRIC
----------------	--------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.52 in
Dimension - Hole Size fraction	5/16
Dimension - Bolt Size fraction	5/16
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	0.36 in
Dimension - L Length Overall mm	53.5 mm
Dimension - B Length inch	1.12 in
Dimension - Bolt Size inch	0.3125
Dimension - Hole Size mm	8.4 mm
Dimension - Hole Size inch	0.38
Dimension - Length Overall inch	2.11 in
Dimension - Strip Length inch	1.18 in
Dimension - Stud Size fraction	5/16

General

Plated	Y
Trade Name	HYLUG™
Die Index	7
UPC	781810638439
Type	Metric Terminals
Material	COPPER
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810638439
UPC 14 Digit GTIN	00781810638439

Logistics

Minimum Pack Quantity	50
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)