



YALB50M10, Compression Terminal

By Burndy
Catalog # [YALB50M10](#)

Copper Compression Terminal



Features

- No inspection window is ideal for more corrosive environments as the barrel transition is not open
- Barrel is designed with internal chamfer at wire entry ensuring smooth insertion of the wire, preventing possible damaging of the wire strands
- Electro-tin plated unless specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with stamping
- Compatible Standards: IEC61238-1, UL 486A-486B, CSA-C22.2 No. 65-03

Application

Metric Wire Termination

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No

Conductor

Conductor Size	50 mm2
Conductor - Material	COPPER
Conductor Type	CLASS 2
Conductor - Copper Str Size	50 mm2

Configuration

Connector Type	METRIC
----------------	--------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.68 in
Dimension - Hole Size fraction	3/8
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	0.42 in
Dimension - L Length Overall mm	65.5 mm
Dimension - B Length inch	1.38 in
Dimension - Bolt Size inch	0.38
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Length Overall inch	2.58 in
Dimension - Strip Length inch	1.46 in
Dimension - Stud Size fraction	3/8

General

Plated	Yes
Trade Name	HYLUG™
Die Index	12
UPC	781810638576
Type	Metric Terminals
Material	COPPER
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810638576
UPC 14 Digit GTIN	00781810638576

Logistics

Carton Quantity	20
-----------------	----

Product Assets

[Catalog \[English\]](#)