

YAV10G61, Seamless Terminal #10 AWG #10 Stud

By Burndy
Catalog # [YAV10G61](#)

SEAMLESS UNINSULATED COMPRESSION HEAVY DUTY RING TONGUE TERMINAL.

Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

Specifications

Certification - cULus	N
Certification - UL Recognized	N
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL467
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Str Aircraft Size	• AN 12 • AN 10
Conductor Size	12 - 10 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
--------------------------------------	---



Connector Type Ring Terminal

Dimensions

Dimension - B Length fraction	2/5 in
Dimension - B Length inch	0.39 in
Dimension - Outside Diameter inch	0.22 in
Dimension - Z inch	0.24 in
Dimension - Pad Width inch	0.34 in
Dimension - Hole Size fraction	1/5
Dimension - Bolt Size fraction	#8 - #10
Dimension - Hole Size inch	0.20 in
Dimension - Hole Size mm	5 mm
Dimension - Stud Size inch	• #8 • #10
Dimension - Length Overall inch	0.80 in
Dimension - Thread Size	-
Dimension - N inch	0.19 in

General

Physical Attribute - Tongue Type	Ring
Trade Name	HYLUG
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Insulation	N
Type	Ring Tongue
UPC 12 Digit	781810099728
UPC 14 Digit GTIN	00781810099728
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810099728

Logistics

Minimum Pack Quantity	10000
Carton Quantity	5000
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)