



YAV1202M10, Compression Terminal

By Burndy
Catalog # YAV1202M10

Copper Compression Terminal



Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping
- Compatible Standards: IEC61238-1, UL 486A-486B, CSA-C22.2 No. 65-03

Application

Metric Wire Termination

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No

Conductor

Conductor - Copper DLO Size Range	N/A
Conductor Size	120 mm2
Conductor - Material	COPPER
Conductor Type	CLASS 2
Conductor - Copper Str Size	120 mm2

Configuration

Number of Pad Holes	2
Connector Type	METRIC

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	29.0 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8

Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.42 in
Dimension - L Length Overall mm	106 mm
Dimension - B Length inch	26.2 in
Dimension - Hole Size mm	10.4 mm
Dimension - Bolt Size inch	0.38
Dimension - Hole Size inch	0.41
Dimension - Length Overall inch	4.18 in
Dimension - Strip Length inch	1.06 in
Dimension - Stud Size fraction	3/8

General

Plated	Y
Trade Name	HYLUG™
Die Index	15
UPC	781810638217
Type	Metric Terminals
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810638217
UPC 14 Digit GTIN	00781810638217

Logistics

Minimum Pack Quantity	10
Pallet Quantity	9600
Carton Quantity	10

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)