



YAV14H32FBOX, Uninsulated Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # [YAV14H32FBOX](#)



Uninsulated Fork Terminal For 16 - 14 AWG

Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Aircraft Size	• AN 20 • AN 18 • AN 16 • AN 14
Conductor - Copper Str Aircraft Size Range	AN 20-AN 14
Conductor - Copper Str Navy Size	• 2 1/2 (1) • 2 1/2 (19) • 2 1/2 (26) • 3 (7) • 4 (1) • 4 (7) • 4 (19) • 4 (41)

Conductor - Copper Str Navy Size Range	2 1/2 (1)-4 (41)
Conductor Size	16 - 14 AWG
Conductor - Copper Str Size	• 20 AWG • 18 AWG • 16 AWG • 14 AWG
Conductor - Copper Str Size Range	20 AWG - 14 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Fork Terminal

Dimensions

Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.27 in
Dimension - Outside Diameter inch	0.17 in
Dimension - Z inch	0.23 in
Dimension - L Length Overall mm	24 mm
Dimension - Pad Width inch	0.30 in
Dimension - Hole Size fraction	3/20
Dimension - Bolt Size fraction	#4 - #6
Dimension - Hole Size inch	0.15 in
Dimension - Strip Length inch	1/4 in
Dimension - Stud Size inch	• #4 • #5 • #6
Cable Insulation Diameter Maximum	0.150 in
Dimension - Length Overall inch	0.96 in
Dimension - N inch	0.19 in

General

Physical Attribute - Tongue Type	Fork
Trade Name	HYLUG™
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Shrouded
Type	Fork Tongue

UPC 12 Digit	781810532683
UPC 14 Digit GTIN	00781810532683
Material	Copper
Plating Type	Tin
UPC	781810532683

Logistics	
Minimum Pack Quantity	100
Carton Quantity	1200

Product Assets

[Catalog \[English\]](#)



A Hubbell brand