



YAV1502M10, Compression Terminal

By Burndy
Catalog # [YAV1502M10](#)

Copper Compression Terminal



Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping
- Compatible Standards: IEC61238-1, UL 486A-486B, CSA-C22.2 No. 65-03

Application

Metric Wire Termination

Specifications

Standards - RoHS Compliance CM
Status

Conductor

Conductor - Material COPPER
Conductor - Copper Str Size 150 mm2
Conductor - Copper DLO Size N/A
Range
Conductor Size 150 mm2
Conductor Type CLASS 2

Configuration

Number of Pad Holes 2
Connector Type METRIC

Current

Voltage Rating 35 kV
Voltage - Maximum 35000

Dimensions

Dimension - Pad Width inch 30.5 in
Package Height 0.000 in
Dimension - Hole Size fraction 3/8
Package Weight 0.000 lb.

Package Length 0.000 in
Package Width 0.000 in
Dimension - L Length Overall 107 mm
mm
Dimension - Hole Size mm 10.4 mm
Dimension - Hole Size inch 0.41
Dimension - Strip Length inch 1.06 in
Dimension - Stud Size fraction 3/8
Dimension - Bolt Size fraction 3/8
Physical Attribute - Tongue Straight
Angle
Dimension - Z inch 0.42 in
Dimension - B Length inch 26.2 in
Dimension - Bolt Size inch 0.38
Dimension - Length Overall 4.20 in
inch

General

Trade Name HYLUG™
Die Index 17
Plated Y
UPC 781810442722
Type Metric Terminals
Material Copper
Plating Type Tin
Finish Type Tin-Plated
UPC 12 Digit 781810442722
UPC 14 Digit GTIN 00781810442722

Logistics

Minimum Pack Quantity 10
Pallet Quantity 9600
Carton Quantity 10

Operational

Temperature Rating 194

Product Assets

[Catalog \[English\]](#)