

YAV16M4, Compression Terminal

By Burndy
Catalog # [YAV16M4](#)

Compression terminal HYLUG™ Copper tubing; 1 Hole; 16 mm2;
M4 Stud; Tin Plating



Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping
- Compatible Standards: IEC61238-1, UL 486A-486B, CSA-C22.2 No. 65-03

Application

Metric Wire Termination

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No

Conductor

Conductor - Copper DLO Size Range	N/A
Conductor Size	16 mm2
Conductor - Material	COPPER
Conductor Type	CLASS 2
Conductor - Copper Str Size	16 mm2

Configuration

Connector Type	METRIC
----------------	--------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.48 in
Dimension - Hole Size fraction	#8
Dimension - Bolt Size fraction	#8
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	0.29 in
Dimension - L Length Overall mm	31.5 mm
Dimension - B Length inch	0.50 in
Dimension - Hole Size mm	4.6 mm
Dimension - Hole Size inch	0.18
Dimension - Length Overall inch	0.09 in
Dimension - Strip Length inch	0.51 in
Dimension - Stud Size fraction	#8

General

Plated	YES
Trade Name	HYLUG™
Die Index	7
UPC	781810637494
Type	Metric Terminals
Material	COPPER
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810637494
UPC 14 Digit GTIN	00781810637494

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalog \[English\]](#)