



YAV14Z5, Uninsulated Flanged Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # [YAV14Z5](#)

Uninsulated Flanged Fork Terminal For 16 - 14 AWG



Features

- Flange fork tongue design allows fast installation as screw only has to be loosened for termination
- Flanges on the end of the fork terminal aid in preventing a slightly loose terminal from becoming fully disconnected from the screw
- Flanges make re-securing a loose terminal easier

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	16 - 14 AWG
Conductor - Copper Str Aircraft Size	• AN 20 • AN 18 • AN 16 • AN 14
Conductor Type	• CU C Flex H-Size • CU C Str-Size
Conductor - Copper Str Size Range	20 AWG - 14 AWG
Conductor - Copper Str Size	• 20 • 18 • 16 • 14

Configuration

Physical Attribute - Number of Holes	1
--------------------------------------	---

Connector Type	Flanged Fork Terminal
----------------	-----------------------

Dimensions

Dimension - Pad Width inch	0.31 in
Dimension - Bolt Size fraction	#4 - #6
Dimension - B Length fraction	1/4 in
Dimension - Z inch	0.13 in
Dimension - B Length inch	0.27 in
Dimension - Length Overall inch	0.86 in
Dimension - Stud Size inch	• #4 • #5 • #6

General

Feature - Barrel Type	Standard
Feature - Barrel Style	Shrouded
Plated	Y
Trade Name	HYLUG™
Physical Attribute - Tongue Type	Flanged Fork
UPC	781810126486
Type	Fork Tongue
Material	Copper
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810126486
UPC 14 Digit GTIN	00781810126486

Logistics

Pallet Quantity	99999
Carton Quantity	1000

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)