

YAV1852M10, Compression Terminal

By Burndy
Catalog # [YAV1852M10](#)

HYLUG™ Copper tubing Compression terminals, 185 mm2, M10
Stud, 2 Holes, Tin Plated



Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping
- Compatible Standards: IEC61238-1, UL 486A-486B, CSA-C22.2 No. 65-03

Application

Metric Wire Termination

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No

Conductor

Conductor - Copper DLO Size Range	N/A
Conductor Size	185 mm2
Conductor - Material	COPPER
Conductor Type	CLASS 2
Conductor - Copper Str Size	185 mm2

Configuration

Connector Type	METRIC
----------------	--------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	32.8 in
Dimension - Hole Size fraction	3/8
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	0.42 in
Dimension - L Length Overall mm	108.2 mm
Dimension - B Length inch	1.06 in
Dimension - Bolt Size inch	0.38
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Length Overall inch	4.26 in
Dimension - Strip Length inch	1.14 in
Dimension - Stud Size fraction	3/8

General

Plated	YES
Trade Name	HYLUG™
Die Index	18
UPC	781810638095
Type	Metric Terminals
Material	COPPER
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810638095
UPC 14 Digit GTIN	00781810638095

Logistics

Pallet Quantity	7680
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)