



YAV2402M20, Compression Terminal

By Burndy
Catalog # [YAV2402M20](#)

Copper Compression Terminal



Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Compatible Standards: IEC61238-1, UL 486A-468B, CSA-C22.2 No. 65-03

Application

Metric Wire Termination

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No

Conductor

Conductor Size	240 mm2
Conductor - Material	COPPER
Conductor Type	CLASS 2

Configuration

Number of Pad Holes	2
Connector Type	METRIC

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.55 in
Package Height	0.000 in
Dimension - Hole Size fraction	7/8
Dimension - Bolt Size fraction	7/8

Physical Attribute - Tongue Angle	Straight
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.89 in
Dimension - L Length Overall mm	141 mm
Dimension - B Length inch	32.3 in
Dimension - Hole Size mm	23.8 mm
Dimension - Bolt Size inch	0.88
Dimension - Hole Size inch	0.94
Dimension - Length Overall inch	5.61 in
Dimension - Strip Length inch	1.30 in
Dimension - Stud Size fraction	7/8

General

Plated	Y
Trade Name	HYLUG™
Die Index	20
UPC	781810638132
Type	Metric Terminals
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810638132
UPC 14 Digit GTIN	00781810638132

Logistics

Minimum Pack Quantity	5
Pallet Quantity	4800
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)