

YAV252M12, Compression Terminal

By Burndy
Catalog # [YAV252M12](#)

HYLUG™ Copper tubing Compression terminals, 25 mm2, M12
Stud, 2 Holes, Tin Plated



Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Compatible Standards: IEC61238-1, UL 486A-468B, CSA-C22.2 No. 65-03

Application

Metric Wire Termination

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No

Conductor

Conductor Size	25 mm2
Conductor - Material	COPPER
Conductor Type	CLASS 2

Configuration

Connector Type	METRIC
----------------	--------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.75 in
----------------------------	---------

Dimension - Hole Size fraction	1/2
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	0.55 in
Dimension - L Length Overall mm	92.5 mm
Dimension - B Length inch	0.50 in
Dimension - Bolt Size inch	0.5
Dimension - Hole Size mm	13.2 mm
Dimension - Hole Size inch	0.53
Dimension - Length Overall inch	3.64 in
Dimension - Strip Length inch	0.51 in
Dimension - Stud Size fraction	1/2

General

Plated	Y
Trade Name	HYLUG™
Die Index	9
UPC	781810637807
Type	Metric Terminals
Material	COPPER
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810637807
UPC 14 Digit GTIN	00781810637807

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalog \[English\]](#)